


**SNMG indexable insert for roughing 30 pieces, HB7130-2, Size: 150612**

**Order data**

|              |               |
|--------------|---------------|
| Order number | GG2950 150612 |
| GTIN         | 4067263092278 |
| Item class   | GGN           |

**Technical description**

|                                      |                    |
|--------------------------------------|--------------------|
| Number of changes/inserts            | 8                  |
| Feed $f$                             | 0.2 - 0.55 mm/rev. |
| Cutting speed $v_c$ main application | 60 - 220 mm/min    |
| Contents                             | 251330 HB7130-2    |
| Cutting depth $a_{p \min}$           | 0.8 mm             |
| Corner radius                        | 1.2 mm             |
| Finishing/roughing assignment        | Roughing           |
| Main application                     | M                  |
| Cutting depth $a_p$                  | 1.5 - 7 mm         |
| ISO code indexable insert            | SNMG 150612        |
| Tool material                        | Carbide            |
| Cutting depth $a_{p \max}$           | 5:25 mm            |
| Quantity                             | 30                 |
| Type                                 | HB7130-2           |

|                    |                              |
|--------------------|------------------------------|
| Cutting conditions | slightly interrupted         |
| Chip breaker       | VG                           |
| Type of product    | Indexable insert for turning |

### **Suitable products**

No Shop URL available for: GG2950 150612