


SNMG indexable insert for roughing 30 pieces, HB7130-2, Size: 150616

Order data

Order number	GG2950 150616
GTIN	4067263092278
Item class	GGN

Technical description

Cutting depth a_p	1.5 - 7 mm
Corner radius	1.6 mm
Contents	251332 HB7130-2
Cutting depth $a_{p \min}$	1.05 mm
Tool material	Carbide
Cutting depth $a_{p \max}$	5:25 mm
Number of changes/inserts	8
Feed f	0.2 - 0.55 mm/rev.
Main application	M
Cutting speed v_c main application	60 - 220 mm/min
Finishing/roughing assignment	Roughing
ISO code indexable insert	SNMG 150616
Quantity	30
Type	HB7130-2

Cutting conditions	slightly interrupted
Chip breaker	VG
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2950 150616