

Garant**Value pack 5 pcs. water pump pliers with ratchet fine adjustment, black****Order data**

Order number	GG6011 250
GTIN	4069515045193
Item class	GGN

Description**Version:**

Box joint designed to prevent fingers being trapped. Push-button **fine step adjustment**, which also allows for quick adjustments directly on the workpiece. Concave profile serrated jaws, self-clamping. The teeth also run against each other in the rear of the jaw for a tight grip. Surface manganese phosphated, polished teeth. Ergonomically shaped handles with non-slip plastic coating.

Standard:

DIN ISO 8976

Material:

Chrome vanadium steel, drop forged.

Supplied with:

5 pcs. water pump pliers No. 706001 size 250.

Technical description

Jaw capacity for pipes	2 in
overall length	250 mm
Hexagon across flats	46 mm
Number of fine adjustment steps	25

Data sheet

Surface	manganese phosphated, polished jaws
Standard	DIN ISO 8976
Type of jaws	concave profile serrated jaws
Material	Chromium vanadium steel
non-sparking	no
Quick adjustment	yes
Stepped fine adjustment	yes
Self-locking	yes
Protection against trapping fingers	yes
Type of product	Pipe wrench and water pump pliers
USP1	5 pcs. water pump pliers with stepped fine adjustment, black

Suitable products

No Shop URL available for: GG6011 250