

Garant**Value pack 5 pcs. carbide-tipped hammer drill SDS-plus****Order data**

Order number	GG6029 8X210
GTIN	4069515045520
Item class	GGN

Description**Version:**

Drill head with square cross-section. **4x90° geometry** with specially developed **equal height tips** and stable shoulders ensure precisely dimensioned holes for professional setting of anchors and secure plug attachment. 4-flute drilling heads for smooth drilling with low vibration and optimum guidance in the drilled hole. **Radially** shaped **reinforcement protection**: prevents jamming when hitting reinforcements and increases the working life. Sturdy **single-piece** carbide head with 4 cutters, inserted as a solid item in the core of the drill. Significantly reduced risk of breakage.

Advantage:

- **Short spiral starts ensure a smooth evacuation of the drill dust.**
- **Wear marks: for evaluation whether the tool is still suitable for drilling holes suitable for insertion of plugs.**
- **4x4 design permits a precise radial run-out and minimise wear and loss of frictional grip.**

Application:

For drilling concrete, natural stone, and masonry – with very high drilling comfort.

Supplied with:

5 pcs. carbide-tipped hammer drill SDS-plus No. 789040 size 8X210.

Technical description

Ø	8 mm
Working length	150 mm
Overall length	210 mm
Tool material	Carbide

Data sheet

Use with impact / without impact	Impact drilling
Shank	SDS Plus
Type of product	Masonry drill
USP1	5 pcs. carbide-tipped hammer drill SDS-plus

Suitable products

No Shop URL available for: GG6029 8X210