



Boring bar steel, right-hand, Shank \varnothing / insert size: 20/11 mm



Order data

Order number	261120 20/11
GTIN	4960664585571
Item class	25U

Description

Version:

Streamlined flutes for improved chip evacuation, reduced tendency to vibrate, stable machining conditions.

Through-coolant: yes

Shank \varnothing D_s : 20 mm

ISO code toolholder: A20R SVUBR/L11

Cutting point / joint: 20 mm

Setting angle κ : 93 degrees

suitable indexable insert: VB.. 1103..

Minimum pre-drill \varnothing D_{min} : 25 mm

Technical description

Minimum pre-drill \varnothing D_{min}	25 mm
suitable indexable insert	VB.. 1103..
Centre offset L_3	18 mm
Insert size	11 mm
Insert screw	269022 6
Cutting point / joint	20 mm
Overhang L_1	80 mm
ISO code toolholder	A20R SVUBR/L11
Overall length L	200 mm
Clamping height L_2	19 mm

Setting angle κ	93 degrees
Shank $\varnothing D_s$	20 mm
Application type	right-hand
Boring depth up to	5xD
Standard	DIN 8024
Through-coolant	yes
Type of product	Boring bar

Accessories

Clamping screw	269409
Clamping screw Type 6	269022 6