

Garant**SNMG indexable insert for roughing 50 pieces, HB7130-2, Size: 120412****Order data**

Order number	GG2951 120412
GTIN	4067263092278
Item class	GGN

Technical description

Main application	M
Cutting depth $a_{p \max}$	4:25 mm
Cutting depth $a_{p \min}$	0.8 mm
Contents	251326 HB7130-2
ISO code indexable insert	SNMG 120412
Cutting speed v_c main application	60 - 220 mm/min
Corner radius	1.2 mm
Finishing/roughing assignment	Roughing
Tool material	Carbide
Quantity	50
Number of changes/inserts	8
Cutting depth a_p	1.5 - 7 mm
Feed f	0.2 - 0.55 mm/rev.

Type	HB7130-2
Cutting conditions	slightly interrupted
Chip breaker	VG
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2951 120412