

Garant**VCGT indexable insert for medium machining 50 pieces, HB7310, Size: 110302****Order data**

Order number	GG3838 110302
GTIN	4067263098683
Item class	GGN

Technical description

Quantity	50
ISO code indexable insert	VCGT 160408
Tool material	Carbide
Main application	N
Contents	261453 HB7310
Finishing/roughing assignment	Finishing
Cutting depth $a_{p \min}$	0.15 mm
Cutting speed v_c main application	350 - 600 mm/min
Number of changes/inserts	2
Corner radius	0.2 mm
Feed f	0.05 - 0.5 mm/rev.
Cutting depth $a_{p \max}$	1.75 mm
Cutting depth a_p	0.1 - 4 mm

Tolerance	G
Type	HB7310
Cutting conditions	continuous
Chip breaker	AM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG3838 110302