

Garant**TCMT indexable insert for medium machining 50 pieces, HB7035-2, Size: 16T308****Order data**

Order number	GG2851 16T308
GTIN	4067263092278
Item class	GGN

Technical description

Cutting depth a_p	0.3 - 2 mm
Number of changes/inserts	3
Contents	260988 HB7035-2
Cutting depth $a_{p \min}$	0.55 mm
Tool material	Carbide
ISO code indexable insert	TCMT 16T308
Finishing/roughing assignment	Finishing
Corner radius	0.8 mm
Feed f	0.08 - 0.3 mm/rev.
Main application	P
Quantity	50
Cutting speed v_c main application	80 - 290 mm/min

Data sheet

Cutting depth $a_{p \max}$	4 mm
Type	HB7035-2
Cutting conditions	heavily interrupted
Chip breaker	SM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2851 16T308