


VNMG indexable insert for finishing 30 pieces, HB7120-1, Size: 160408

Order data

Order number	GG2964 160408
GTIN	4067263092278
Item class	GGN

Technical description

Cutting speed v_c main application	90 - 290 mm/min
Cutting depth $a_{p \text{ min}}$	0.55 mm
Tool material	Carbide
Cutting depth $a_{p \text{ max}}$	2.5 mm
ISO code indexable insert	VNMG 160408
Contents	251734 HB7120-1
Number of changes/inserts	4
Feed f	0.05 - 0.4 mm/rev.
Cutting depth a_p	0.3 - 2 mm
Main application	M
Finishing/roughing assignment	Finishing
Corner radius	0.8 mm
Quantity	30
Type	HB7120-1

Cutting conditions	continuous
Chip breaker	VS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2964 160408