

Garant**VCGT indexable insert for medium machining 50 pieces, HB7310, Size: 110304****Order data**

Order number	GG3838 110304
GTIN	4067263098706
Item class	GGN

Technical description

Main application	N
Contents	261454 HB7310
Finishing/roughing assignment	Roughing
Finishing/roughing assignment	Finishing
Cutting depth $a_{p \max}$	1.75 mm
Corner radius	0.4 mm
Number of changes/inserts	2
ISO code indexable insert	VCGT 110304
Cutting depth $a_{p \min}$	0.25 mm
Cutting speed v_c main application	350 - 600 mm/min
Quantity	50
Tool material	Carbide
Feed f	0.05 - 0.5 mm/rev.

Data sheet

Cutting depth a_p	0.1 - 4 mm
Tolerance	G
Type	HB7310
Cutting conditions	continuous
Chip breaker	AM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG3838 110304