


VBMT indexable insert for finishing 30 pieces, HB7010-2, Size: 110304

Order data

Order number	GG2852 110304
GTIN	4067263092278
Item class	GGN

Technical description

Main application	P
Contents	261144 HB7010-2
Cutting speed v_c main application	150 - 500 mm/min
Number of changes/inserts	2
Cutting depth a_p	0.2 - 1.5 mm
Finishing/roughing assignment	Finishing
ISO code indexable insert	VBMT 110304
Tool material	Carbide
Cutting depth $a_{p \min}$	0.25 mm
Cutting depth $a_{p \max}$	1.75 mm
Feed f	0.07 - 0.25 mm/rev.
Corner radius	0.4 mm
Quantity	30
Type	HB7010-2

Data sheet

Cutting conditions	continuous
Chip breaker	SS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2852 110304