

**VNMG indexable insert for finishing 30 pieces, HB7140-2, Size: 160408****Order data**

Order number	GG2966 160408
GTIN	4067263092278
Item class	GGN

Technical description

Contents	251734 HB7140-2
Coating	coated
Finishing/roughing assignment	Finishing
Corner radius	0.8 mm
Quantity	30
ISO code indexable insert	VNMG 160408
Cutting depth $a_{p \max}$	2.5 mm
Number of changes/inserts	4
Cutting speed v_c main application	70 - 230 mm/min
Cutting depth $a_{p \min}$	0.55 mm
Tool material	Carbide
Main application	M
Cutting depth a_p	0.3 - 2 mm
Feed f	0.05 - 0.4 mm/rev.

Type	HB7140-2
Cutting conditions	heavily interrupted
Chip breaker	VS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2966 160408