

**Garant**

**Thread turning insert, internal, full profile 60°, left-hand, L1 = 16 mm, Ø Dmin / Pitch: 3,2/0,7mm**


**Order data**

Order number	270410 3,2/0,7
GTIN	4045197467546
Item class	211

**Description**
**Application:**

For cutter holder No. 270200 – 270204.

Thread type: MF

Thread type: MF

Tolerance class: DIN 13 6H

Shank Ø d: 4 mm

Tip centre offset L<sub>3</sub>: 0.9 mm

Thread tip-face distance Y: 0.5 mm

Minimum advance h<sub>min</sub>: 0.41 mm

**Technical description**

Tolerance class	DIN 13 6H
Tip centre offset L <sub>3</sub>	0.9 mm
Minimum Ø D <sub>min</sub>	3.2 mm
Shank Ø d	4 mm
Minimum advance h <sub>min</sub>	0.41 mm
Thread tip-face distance Y	0.5 mm
Overhang L <sub>1</sub>	16 mm
Product name attribute	L <sub>1</sub> = 16 mm
Flank angle	60 °
Thread type	M

Thread type	M-LH
Thread type	MF-LH
Thread type	MF
Type of product	Thread turning insert

## User data

	Suitability	V <sub>c</sub>	ISO code
Alu plastics	suitable only under restricted conditions	200 m/min	N
Aluminium (short chipping)	suitable only under restricted conditions	200 m/min	N
Alu > 10% Si	suitable only under restricted conditions	150 m/min	N
Steel < 500 N/mm <sup>2</sup>	suitable	160 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	150 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	150 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	80 m/min	P
Steel < 1400 N/mm <sup>2</sup>	suitable	60 m/min	P
Steel < 55 HRC	suitable only under restricted conditions	30 m/min	H
INOX < 900 N/mm <sup>2</sup>	suitable	90 m/min	M
INOX > 900 N/mm <sup>2</sup>	suitable	60 m/min	M
Ti > 850 N/mm <sup>2</sup>	suitable only under restricted conditions	30 m/min	S
GG(G)	suitable	90 m/min	K
CuZn	suitable	150 m/min	N
continuous	suitable		
wet maximum	suitable		