


VBMT indexable insert for finishing 30 pieces, HB7035-2, Size: 110304

Order data

Order number	GG2854 110304
GTIN	4067263092278
Item class	GGN

Technical description

Feed f	0.07 - 0.25 mm/rev.
Tool material	Carbide
Corner radius	0.4 mm
Number of changes/inserts	2
Cutting depth $a_{p \min}$	0.25 mm
Finishing/roughing assignment	Finishing
Main application	P
Cutting depth $a_{p \max}$	1.75 mm
ISO code indexable insert	VBMT 110304
Cutting speed v_c main application	120 - 350 mm/min
Contents	261144 HB7035-2
Cutting depth a_p	0.2 - 1.5 mm
Quantity	30
Type	HB7035-2

Cutting conditions	heavily interrupted
Chip breaker	SS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2854 110304