

**Value pack CNMG indexable insert roughing 30 pieces HBT020****Order data**

Order number	GG3904 160608
GTIN	4067263092773
Item class	GGN

Technical description

ISO code indexable insert	CNMG 160608
Cutting depth $a_{p \max}$	5.5 mm
Main application	P
Finishing/roughing assignment	Roughing
Cutting depth $a_{p \min}$	0.55 mm
Cutting speed v_c main application	80 - 260 mm/min
Tool material	Carbide
Cutting depth a_p	1.8 - 6 mm
Coating	TiCN
Feed f	0.2 - 0.6 mm/rev.
Contents	250220 HBT020
Number of changes/inserts	4
Corner radius	0.8 mm
Quantity	30
Type	HBT020
Cutting conditions	slightly interrupted
Chip breaker	PR
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG3904 160608
