

**TCMT indexable insert for finishing 30 pieces, HB7130-2, Size: 16T304****Order data**

Order number	GG3541 16T304
GTIN	4067263092278
Item class	GGN

Technical description

Tool material	Carbide
Cutting depth a_p	0.2 - 1.5 mm
Contents	260956 HB7130-2
Corner radius	0.4 mm
Feed f	0.1 - 0.3 mm/rev.
ISO code indexable insert	TCMT 16T304
Finishing/roughing assignment	Finishing
Cutting depth $a_{p \min}$	0.25 mm
Number of changes/inserts	3
Main application	M
Cutting depth $a_{p \max}$	4 mm
Cutting speed v_c main application	80 - 270 mm/min
Quantity	30
Type	HB7130-2

Cutting conditions	slightly interrupted
Chip breaker	VS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG3541 16T304