



CNMG indexable insert for roughing 50 pieces, HBT020, Size: 160612

Order data

Order number	GG3905 160612
GTIN	4067263092803
Item class	GGN

Technical description

Contents	250221 HBT020
Main application	P
Coating	TiCN
ISO code indexable insert	CNMG 160612
Finishing/roughing assignment	Roughing
Cutting depth $a_{p \max}$	5.5 mm
Corner radius	1.2 mm
Cutting depth a_p	1.8 - 6 mm
Number of changes/inserts	4
Tool material	Carbide
Feed f	0.2 - 0.6 mm/rev.
Cutting speed v_c main application	80 - 260 mm/min
Cutting depth $a_{p \min}$	0.8 mm
Quantity	50
Type	HBT020
Cutting conditions	slightly interrupted
Chip breaker	PR
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG3905 160612
