

Garant**VNMG indexable insert for finishing 50 pieces, HB7140-2, Size: 160408****Order data**

Order number	GG2969 160408
GTIN	4067263092278
Item class	GGN

Technical description

Finishing/roughing assignment	Finishing
Main application	M
Tool material	Carbide
Cutting depth $a_{p \min}$	0.55 mm
Corner radius	0.8 mm
Contents	251734 HB7140-2
Quantity	50
Number of changes/inserts	4
Cutting depth $a_{p \max}$	2.5 mm
ISO code indexable insert	VNMG 160408
Feed f	0.05 - 0.4 mm/rev.
Coating	coated
Cutting speed v_c main application	70 - 230 mm/min

Data sheet

Cutting depth a_p	0.3 - 2 mm
Type	HB7140-2
Cutting conditions	heavily interrupted
Chip breaker	VS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2969 160408