


VBMT indexable insert for finishing 50 pieces, HB7020-2, Size: 160404

Order data

Order number	GG2856 160404
GTIN	4067263092278
Item class	GGN

Technical description

Cutting depth $a_{p \min}$	0.25 mm
Corner radius	0.4 mm
Finishing/roughing assignment	Finishing
ISO code indexable insert	VBMT 160404
Tool material	Carbide
Cutting speed v_c main application	140 - 400 mm/min
Cutting depth $a_{p \max}$	2.5 mm
Contents	261152 HB7020-2
Cutting depth a_p	0.2 - 1.5 mm
Feed f	0.07 - 0.25 mm/rev.
Quantity	50
Number of changes/inserts	2
Main application	P

Type	HB7020-2
Cutting conditions	slightly interrupted
Chip breaker	SS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2856 160404