


VBMT indexable insert for finishing 50 pieces, HB7035-2, Size: 110302

Order data

Order number	GG2857 110302
GTIN	4067263092278
Item class	GGN

Technical description

Quantity	50
Cutting speed v_c main application	120 - 350 mm/min
Contents	261142 HB7035-2
Corner radius	0.2 mm
Finishing/roughing assignment	Finishing
Feed f	0.07 - 0.25 mm/rev.
ISO code indexable insert	VBMT 110302
Cutting depth $a_{p \max}$	1.75 mm
Main application	P
Tool material	Carbide
Cutting depth $a_{p \min}$	0.15 mm
Cutting depth a_p	0.2 - 1.5 mm
Number of changes/inserts	2

Type	HB7035-2
Cutting conditions	heavily interrupted
Chip breaker	SS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2857 110302