

Garant**VBMT indexable insert for finishing 50 pieces, HB7035-2, Size: 160404****Order data**

Order number	GG2857 160404
GTIN	4067263092278
Item class	GGN

Technical description

Cutting depth $a_{p \min}$	0.25 mm
Finishing/roughing assignment	Finishing
Cutting depth a_p	0.2 - 1.5 mm
Number of changes/inserts	2
Corner radius	0.4 mm
Contents	261152 HB7035-2
Quantity	50
Tool material	Carbide
ISO code indexable insert	VBMT 160404
Main application	P
Cutting speed v_c main application	120 - 350 mm/min
Cutting depth $a_{p \max}$	2.5 mm
Feed f	0.07 - 0.25 mm/rev.

Type	HB7035-2
Cutting conditions	heavily interrupted
Chip breaker	SS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2857 160404