

**Garant****VBMT indexable insert for medium machining 50 pieces, HB7020-2, Size: 110304****Order data**

|              |               |
|--------------|---------------|
| Order number | GG2862 110304 |
| GTIN         | 4067263095866 |
| Item class   | GGN           |

**Technical description**

|                                      |                    |
|--------------------------------------|--------------------|
| Corner radius                        | 0.4 mm             |
| ISO code indexable insert            | VBMT 110304        |
| Cutting depth $a_{p \max}$           | 1.75 mm            |
| Number of changes/inserts            | 2                  |
| Main application                     | P                  |
| Cutting depth $a_{p \min}$           | 0.25 mm            |
| Finishing/roughing assignment        | Finishing          |
| Cutting depth $a_p$                  | 0.3 - 2 mm         |
| Feed $f$                             | 0.08 - 0.3 mm/rev. |
| Tool material                        | Carbide            |
| Contents                             | 261224 HB7020-2    |
| Cutting speed $v_c$ main application | 110 - 350 mm/min   |

Data sheet

|                    |                              |
|--------------------|------------------------------|
| Quantity           | 50                           |
| Type               | HB7020-2                     |
| Cutting conditions | slightly interrupted         |
| Chip breaker       | SM                           |
| Type of product    | Indexable insert for turning |

**Suitable products**

No Shop URL available for: GG2862 110304