

Garant**VBMT indexable insert for medium machining 50 pieces, HB7020-2, Size: 160404****Order data**

Order number	GG2862 160404
GTIN	4067263095880
Item class	GGN

Technical description

Number of changes/inserts	2
Contents	261232 HB7020-2
Feed f	0.08 - 0.3 mm/rev.
ISO code indexable insert	VBMT 160404
Cutting speed v_c main application	110 - 350 mm/min
Cutting depth $a_{p \min}$	0.25 mm
Cutting depth a_p	0.3 - 2 mm
Cutting depth $a_{p \max}$	2.5 mm
Tool material	Carbide
Corner radius	0.4 mm
Finishing/roughing assignment	Finishing
Main application	P

Data sheet

Quantity	50
Type	HB7020-2
Cutting conditions	slightly interrupted
Chip breaker	SM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2862 160404