


WNMG indexable insert for finishing 30 pieces, HB7140-2, Size: 060408

Order data

Order number	GG2978 060408
GTIN	4067263092278
Item class	GGN

Technical description

Cutting depth a_p	0.3 - 2 mm
Cutting depth $a_{p \min}$	0.55 mm
Feed f	0.1 - 0.4 mm/rev.
Cutting speed v_c main application	70 - 230 mm/min
ISO code indexable insert	WNMG 060408
Main application	M
Tool material	Carbide
Cutting depth $a_{p \max}$	2 mm
Contents	251954 HB7140-2
Coating	coated
Finishing/roughing assignment	Finishing
Quantity	30
Corner radius	0.8 mm
Number of changes/inserts	6

Data sheet

Type	HB7140-2
Cutting conditions	heavily interrupted
Chip breaker	VS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2978 060408