


VBMT indexable insert for finishing 30 pieces, HB7120-1, Size: 110302

Order data

Order number	GG3552 110302
GTIN	4067263092278
Item class	GGN

Technical description

ISO code indexable insert	VBMT 110302
Cutting depth $a_{p \min}$	0.15 mm
Tool material	Carbide
Finishing/roughing assignment	Finishing
Cutting depth $a_{p \max}$	1.75 mm
Corner radius	0.2 mm
Contents	261142 HB7120-1
Cutting speed v_c main application	90 - 290 mm/min
Main application	M
Feed f	0.1 - 0.3 mm/rev.
Number of changes/inserts	2
Cutting depth a_p	0.2 - 1.5 mm
Quantity	30
Type	HB7120-1

Cutting conditions	continuous
Chip breaker	VS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG3552 110302