

Garant**VBMT indexable insert for finishing 30 pieces, HB7120-1, Size: 160404****Order data**

Order number	GG3552 160404
GTIN	4067263092278
Item class	GGN

Technical description

Tool material	Carbide
Contents	261152 HB7120-1
Cutting depth a_p	0.2 - 1.5 mm
Corner radius	0.4 mm
Feed f	0.1 - 0.3 mm/rev.
Main application	M
Number of changes/inserts	2
Cutting depth $a_{p \max}$	2.5 mm
Cutting speed v_c main application	90 - 290 mm/min
ISO code indexable insert	VBMT 160404
Cutting depth $a_{p \min}$	0.25 mm
Finishing/roughing assignment	Finishing
Quantity	30
Type	HB7120-1

Cutting conditions	continuous
Chip breaker	VS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG3552 160404