

**HOLEX®**
**Side lock arbor Form AD, SK 40 A = 160, Clamping range  $\varnothing$  D1: 16 mm**

**Order data**

|              |               |
|--------------|---------------|
| Order number | 300280 16     |
| GTIN         | 4045197143945 |
| Item class   | 32A           |

**Description**
**Version:**

With Balluffchip bore.

**Application:**

For clamping tools with side flat to DIN 1835 B and DIN 6535 HB.

**Optional extras:**

Pull studs (PS) No. 308600 – 308806. Pull stud wrenches No. 308820; 308835.

External  $\varnothing$  D: 48 mm

Spare clamping screw 309900: 16

**Technical description**

|                                       |                      |
|---------------------------------------|----------------------|
| Clamping $\varnothing$ D <sub>1</sub> | 16 mm                |
| Spare clamping screw 309900           | 16                   |
| External $\varnothing$ D              | 48 mm                |
| Adapter                               | SK 40 A = 160        |
| Norm                                  | DIN 6359             |
| Arbor standard                        | DIN 69871            |
| Arbor standard                        | ISO 7388-1           |
| Shape                                 | AD                   |
| Balance quality G at rotational speed | G 6.3 at 15,000 rpm  |
| Concentricity                         | $\leq 3 \mu\text{m}$ |

Machining strategy

HPC

## Accessories

Torque insert for Pull studs to SO 7388 suitable for steep tapers 40 SK

308812 40

Pull stud wrench for Pull studs to DIN 69872 suitable for steep tapers 40 SK

308820 40

Pull stud, 18CrNiMo7 Form A suitable for steep tapers 40

308605 40

Special pull stud with internal thread suitable for steep tapers 40

308740 40

Pull stud sealed, form B suitable for steep tapers 40

308650 40

Pull stud 45° sealed suitable for steep tapers 40

308765 40

Pull stud sealed, form B suitable for steep tapers 40

308620 40

Pull stud stud sealed, form A suitable for steep tapers 40

308610 40

Pull stud sealed suitable for steep tapers 40

308635 40

Pull stud Mazak sealed, form A suitable for steep tapers 40M

308670 40M

Pull stud Form B suitable for steep tapers 40

308640 40

Pull stud Hurco 90° with fit sealed suitable for steep tapers 40

308806 40

Pull stud Hurco 45° with fit sealed suitable for steep tapers 40

308802 40

Pull stud 90° sealed suitable for steep tapers 40

308790 40

Pull stud 45° sealed suitable for steep tapers 40

308760 40

Pull stud Mori-Seiki, sealed, form A suitable for steep tapers 40

308630 40

Pull stud, 18CrNiMo7 sealed, form B suitable for steep tapers 40

308615 40

Pull stud Mori-Seiki, sealed, form A suitable for steep tapers 40

308625 40

Pull stud 60° sealed suitable for steep tapers 40

308785 40

|   |           |
|---|-----------|
| Special pull stud with no internal thread sealed suitable for steep tapers 40 | 308700 40 |
| Special pull stud with no internal thread sealed suitable for steep tapers 40 | 308720 40 |
| Pull stud Form A suitable for steep tapers 40                                 | 308600 40 |
| Pull stud sealed suitable for steep tapers 40                                 | 308660 40 |
| Torque insert for Pull studs to DIN 69872 suitable for steep tapers 40 SK     | 308810 40 |
| Pull stud 90° sealed suitable for steep tapers 40                             | 308795 40 |
| Pull stud Hurco 45° with bore and fit sealed suitable for steep tapers 40     | 308801 40 |
| Pull stud wrench for Pull studs to ISO 7388 suitable for steep tapers 40 SK   | 308830 40 |