



LED-EX torch with batteries, Type: 3AA



Order data

Order number	081521 3AA
GTIN	032705100143
Item class	08C

Description

Version:

Explosion-proof torch, tested to the applicable ATEX guidelines.

High-performance LED lamps shock-resistant, dust-proof and waterproof.

With **LED reflector technology. LED hand lamp and helmet lamp made of flame-retardant materials.** Wide spot beam, ideal for fire fighting and extreme cold.

Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

Technical description

Illumination time	8 h
Head Ø	35 mm
Colour of housing	GREY
ATEX zone	zone 20
ATEX zone	zone 0
Battery type	Mignon, AA
Number of batteries contained	3
Illumination	150 lm
Weight	139 g
IP Index of Protection	IP 67

Overall length	135 mm
Tool properties	Suitable for EX areas
Illumination range	95 m
Power supply	Battery-powered
Type of product	Flashlight

Accessories

Lithium-metal batteries International size LR6	081559 LR6
Alkaline-manganese batteries International size LR6	081554 LR6
Alkaline-manganese batteries International size LR6	081551 LR6
Alkaline-manganese batteries International size LR6	081561 LR6
Alkaline-manganese batteries International size LR6	081553 LR6
Alkaline-manganese batteries International size LR6	081552 LR6