

Garant**VB.T 160408, Grade: HU7310**

Order data

Order number	261234 HU7310
GTIN	4045197696274
Item class	21G

Description

VB.T 160408 HU7310 Grade: HU7310
Chip breaker: AM
Tolerance: G
Cutting depth a_p : 0.1 - 4 mm
Feed f : 0.05 - 0.5 mm/rev.
Cutting speed v_c main application: 350 - 600 m/min

Technical description

Cutting speed v_c main application	350 - 600 m/min
Cutting depth a_p	0.1 - 4 mm
Corner radius	0.8 mm
Cutting conditions	continuous
Main application	N
Feed f	0.05 - 0.5 mm/rev.

Chip breaker	AM
Grade	HU7310
Finishing/roughing assignment	Semi-roughing
Tool material	Carbide
Coating	uncoated
ISO code indexable insert	VBGT 160408
Number of changes/inserts	2
Tolerance	G
Type of product	Indexable insert for turning