

Garant
Side lock arbor Form ADB, SK 40 A = 130, Clamping range Ø D1: 16mm

Order data

Order number	300270 16
GTIN	4045197283030
Item class	31A

Description
Version:

With Balluff/RFID chip bore.

GARANT –

All shanks hard turned (for smooth cutting action!). Balancing quality G 2.5 / G 25,000 rpm

Application:

For clamping tools with side flat to DIN 1835 B and DIN 6535 HB.

Optional extras:

Pull studs (PS) No. 308600 – 308806. Pull stud wrenches No. 308820; 308835.

Technical description

Clamping Ø D ₁	16 mm
Overhang dimension A	130 mm
Spare clamping screw No. 30 9900	16
External Ø D	48 mm
Adapter	SK 40 A = 130
Standard	DIN 6359
Arbor standard	ISO 7388-1
Shape	ADB
Balance quality G at rotational speed	G 2.5 at 25,000 rpm

Concentricity	≤ 3 µm
Machining strategy	HPC
Type of product	Side lock arbor

Accessories

Hurco 45° pull stud with 4-mm bore and fitsealed suitable for steep tapers 40	308801 40
Special pull stud with no internal threadsealed suitable for steep tapers 40	308700 40
Pull stud 90°sealed suitable for steep tapers 40	308795 40
Pull studsealed suitable for steep tapers 40	308635 40
Pull studForm A suitable for steep tapers 40	308600 40
Pull studsealed, form B suitable for steep tapers 40	308620 40
Pull stud, 18CrNiMo7sealed, form B suitable for steep tapers 40	308615 40
Pull studsealed, form A suitable for steep tapers 40	308610 40
Pull stud 90°sealed suitable for steep tapers 40	308790 40
Pull stud, 18CrNiMo7Form A suitable for steep tapers 40	308605 40
Wrench for pull studsISO 7388 suitable for ISO taper size 40	308830 40
Special pull stud with internal thread suitable for steep tapers 40	308740 40
Pull stud 45°sealed suitable for steep tapers 40	308765 40
Pull stud Hurco 90° with fitsealed suitable for steep tapers 40	308806 40
Pull studsealed, form B suitable for steep tapers 40	308650 40
Wrench for pull studsDIN ISO 7388-1 (formerly DIN 69872) suitable for ISO taper size 40	308820 40
Pull studMori-Seiki, sealed, form A suitable for steep tapers 40	308625 40
	308630 40

Pull studMori-Seiki, sealed, form A suitable for steep tapers 40

Pull stud 60°sealed suitable for steep tapers 40

308785 40

Pull stud 45°sealed suitable for steep tapers 40

308760 40

Pull studsealed suitable for steep tapers 40

308660 40

Pull studMazak, form A suitable for steep tapers 40M

308670 40M

Pull studForm B suitable for steep tapers 40

308640 40

Pull stud Hurco 45° with fitsealed suitable for steep tapers 40

308802 40

Spare clamping screw for chucks with clamping \varnothing D1 16 mm

309900 16