

Garant
**Combination side lock arbor, slim Form ADB, SK 40 A = 100, Clamping range
 Ø D1: 10mm**

Order data

Order number	300422 10
GTIN	4045197287625
Item class	31A

Description
Version:

- **Hole tolerance D₁ in H4 (tighter than DIN).**

Shanks hard turned (smooth cutting action!). With RFID/Balluffchip bore.

Application:

For clamping tools with plain shank to DIN 1835 Form B + E and DIN 6535 Form HB + HE.

Supplied with:

With ball-jointed clamping screw **for Weldon and Whistle Notch systems** and through drilled back stop screw.

Optional extras:

Pull studs (PS) No. 308600 – 308806, PS pull stud wrenches No. 308820 – 308835, spare clamping screw 309905 M6, 309905 M8.

Technical description

Clamping Ø D ₁	10 mm
Ø D ₂	16 mm
Ø D ₃	21 mm
Overhang dimension A	100 mm
External Ø D	32.28 mm
Adapter	SK 40 A = 100

Standard	DIN 6359
Arbor standard	ISO 7388-1
Shape	ADB
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 3 µm
Machining strategy	HPC
Type of product	Side lock arbor

Accessories

Wrench for pull studs ISO 7388 suitable for ISO taper size 40	308830 40
Pull stud, 18CrNiMo7sealed, form B suitable for steep tapers 40	308615 40
Pull studsealed, form A suitable for steep tapers 40	308610 40
Pull studMori-Seiki, sealed, form A suitable for steep tapers 40	308630 40
Pull studForm A suitable for steep tapers 40	308600 40
Special pull stud with no internal threadsealed suitable for steep tapers 40	308700 40
Pull stud 90°sealed suitable for steep tapers 40	308790 40
Pull studsealed, form B suitable for steep tapers 40	308620 40
Pull studForm B suitable for steep tapers 40	308640 40
Pull stud 90°sealed suitable for steep tapers 40	308795 40
Pull stud 60°sealed suitable for steep tapers 40	308785 40
Pull stud 45°sealed suitable for steep tapers 40	308760 40
Pull studMazak, form A suitable for steep tapers 40M	308670 40M
Pull stud Hurco 90° with fitsealed suitable for steep tapers 40	308806 40
Special pull stud with internal thread suitable for steep tapers 40	308740 40

Pull stud Hurco 45° with fitsealed suitable for steep tapers 40	308802 40
Pull studsealed suitable for steep tapers 40	308660 40
Pull stud, 18CrNiMo7Form A suitable for steep tapers 40	308605 40
Wrench for pull studsDIN ISO 7388-1 (formerly DIN 69872) suitable for ISO taper size 40	308820 40
Pull studsealed suitable for steep tapers 40	308635 40
Pull studsealed, form B suitable for steep tapers 40	308650 40
Hurco 45° pull stud with 4-mm bore and fitsealed suitable for steep tapers 40	308801 40
Pull stud 45°sealed suitable for steep tapers 40	308765 40
Pull studMori-Seiki, sealed, form A suitable for steep tapers 40	308625 40