

Garant
Side lock arbor Form ADB, SK 50 A = 160, Clamping range Ø D1: 12mm

Order data

Order number	300350 12
GTIN	4045197284181
Item class	31A

Description
Version:

With Balluff/RFID chip bore.

GARANT –

All shanks hard turned (for smooth cutting action!). Balancing quality G 2.5 / G 25,000 rpm

Application:

For clamping tools with side flat to DIN 1835 B and DIN 6535 HB.

Optional extras:

Pull studs (PS) No. 308600 – 308806. Pull stud wrenches No. 308820; 308835.

Technical description

Clamping Ø D ₁	12 mm
Spare clamping screw No. 30 9900	12
Overhang dimension A	160 mm
External Ø D	42 mm
Adapter	SK 50 A = 160
Standard	DIN 6359
Arbor standard	ISO 7388-1
Shape	ADB
Balance quality G at rotational speed	G 2.5 at 25,000 rpm

Concentricity	≤ 3 µm
Machining strategy	HPC
Type of product	Side lock arbor

Accessories

Pull studsealed, form B suitable for steep tapers 50	308620 50
Pull studForm A suitable for steep tapers 50	308600 50
Pull stud, 18CrNiMo7sealed, form B suitable for steep tapers 50	308615 50
Pull stud 45°sealed suitable for steep tapers 50	308765 50
Pull stud 45°sealed suitable for steep tapers 50	308760 50
Pull studsealed, form A suitable for steep tapers 50	308610 50
Pull studForm B suitable for steep tapers 50	308640 50
Pull studsealed suitable for steep tapers 50	308660 50
Pull studsealed, form B suitable for steep tapers 50	308650 50
Pull stud 60°sealed suitable for steep tapers 50	308785 50
Wrench for pull studsISO 7388 suitable for ISO taper size 50	308830 50
Pull stud 90°sealed suitable for steep tapers 50	308790 50
Special pull stud with internal thread suitable for steep tapers 50	308740 50
Pull stud 90°sealed suitable for steep tapers 50	308795 50
Wrench for pull studsDIN ISO 7388-1 (formerly DIN 69872) suitable for ISO taper size 50	308820 50
Special pull stud with no internal threadsealed suitable for steep tapers 50	308720 50
Pull stud, 18CrNiMo7Form A suitable for steep tapers 50	308605 50
Spare clamping screw for chucks with clamping Ø D1 12 mm	309900 12