

Garant**VCMT indexable insert for finishing 50 pieces, HB7010-2, Size: 110304****Order data**

Order number	GG2867 110304
GTIN	4067263092278
Item class	GGN

Technical description

Cutting speed v_c main application	150 - 500 mm/min
Cutting depth $a_{p \min}$	0.25 mm
Tool material	Carbide
Quantity	50
Main application	P
Feed f	0.07 - 0.25 mm/rev.
Tolerance	M
ISO code indexable insert	VCMT 110304
Cutting depth $a_{p \max}$	1.75 mm
Cutting depth a_p	0.2 - 1.5 mm
Number of changes/inserts	2
Finishing/roughing assignment	Finishing
Contents	261366 HB7010-2

Data sheet

Corner radius	0.4 mm
Type	HB7010-2
Cutting conditions	continuous
Chip breaker	SS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2867 110304