

Garant**VCMT indexable insert for finishing 50 pieces, HB7010-2, Size: 160402****Order data**

Order number	GG2867 160402
GTIN	4067263092278
Item class	GGN

Technical description

Number of changes/inserts	2
ISO code indexable insert	VCMT 160402
Contents	261370 HB7010-2
Feed f	0.07 - 0.25 mm/rev.
Cutting depth $a_{p \min}$	0.15 mm
Tool material	Carbide
Main application	P
Corner radius	0.2 mm
Finishing/roughing assignment	Finishing
Tolerance	M
Cutting depth a_p	0.2 - 1.5 mm
Cutting depth $a_{p \max}$	2.5 mm
Cutting speed v_c main application	150 - 500 mm/min

Data sheet

Quantity	50
Type	HB7010-2
Cutting conditions	continuous
Chip breaker	SS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2867 160402