

Garant
ER collet chuck Form ADB, SK 40 A = 70, for ER collet size: 40

Order data

Order number	300470 40
GTIN	4045197284679
Item class	31A

Description
Version:

Taper ground internally and externally. With Balluff/RFID chip bore.

GARANT –

- **Balancing quality G2.5 / 25,000 rpm**
- **All shanks hard turned (for smooth running!).**
- **GARANT precision clamping nut, fine balanced (G 2.5 / 25,000 rpm) and coated, giving high clamping force and low wear.**
- **Through bored.**

Application:

For clamping tools with plain shank in collets to DIN 6499 - Form A and B.

Supplied with:

Clamping nut

Optional extras:

Pull studs (PS) No. 308600 – 308806, PS pull stud wrenches No.308820 – 308835, ER chuck key No. 309680 – 613300, ER collets No. 308901 – 309449, ER clamping nuts No. 309615 (for sealing rings), sealing rings No. 309625 – 309645 (for No. 309615).

Technical description

Clamping range	3 - 26 mm
Spare HOLEX nut No. 309580	40
Spare GARANT high-speed clamping nut No. 309610	40

for ER collets	40
Overhang dimension A	70 mm
External Ø D	63 mm
Adapter	SK 40 A = 70
Arbor standard	ISO 7388-1
Shape	ADB
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 3 µm
Machining strategy	HSC
Balluffchip bore	yes
Type of product	Collet chuck

Accessories

Wrench for pull studs DIN ISO 7388-1 (formerly DIN 69872) suitable for ISO taper size 40	308820 40
ER collet Nominal clamping Ø d 14 mm	309040 14
ER collet Nominal clamping Ø d 24 mm	308990 24
Special pull stud with no internal thread sealed suitable for steep tapers 40	308700 40
ER collet Nominal clamping Ø d 25 mm	308990 25
ER collet Nominal clamping Ø d 7 mm	309040 7
ER collet Nominal clamping Ø d 12 mm	308990 12
Pull stud sealed, form B suitable for steep tapers 40	308650 40
ER collet Nominal clamping Ø d 17 mm	308990 17
ER collet Nominal clamping Ø d 16 mm	308990 16
ER collet HP Nominal clamping Ø d 26 mm	309379 26
ER collet Nominal clamping Ø d 9 mm	309040 9
Pull stud sealed suitable for steep tapers 40	308660 40

ER collet Nominal clamping Ø d 24 mm	309040 24
ER collet HP Nominal clamping Ø d 10 mm	309379 10
ER collet Nominal clamping Ø d 14 mm	308990 14
ER collet Nominal clamping Ø d 10 mm	308990 10
ER collet Nominal clamping Ø d 26 mm	309040 26
Pull studMazak, form A suitable for steep tapers 40M	308670 40M
ER collet for machine tapswith seal Nominal clamping Ø d 9 mm	309419 9
ER collet HP Nominal clamping Ø d 13 mm	309379 13
Pull stud, 18CrNiMo7sealed, form B suitable for steep tapers 40	308615 40
Special pull stud with internal thread suitable for steep tapers 40	308740 40
ER collet Nominal clamping Ø d 4 mm	309040 4
ER collet Nominal clamping Ø d 25 mm	309040 25
Pull stud 45°sealed suitable for steep tapers 40	308760 40
ER collet Nominal clamping Ø d 20 mm	309040 20
ER collet Nominal clamping Ø d 5 mm	309040 5
ER collet for machine tapswith seal Nominal clamping Ø d 18 mm	309419 18
ER collet Nominal clamping Ø d 4 mm	308990 4
Pull studForm A suitable for steep tapers 40	308600 40
ER colletwith seal Nominal clamping Ø d 20 mm	308992 20
ER colletwith seal Nominal clamping Ø d 25 mm	308992 25
ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 10 mm	309449 10
Hurco 45° pull stud with 4-mm bore and fitsealed suitable for steep tapers 40	308801 40
Pull studForm B suitable for steep tapers 40	308640 40
ER collet Nominal clamping Ø d 6 mm	308990 6
Pull stud 60°sealed suitable for steep tapers 40	308785 40

ER collet Nominal clamping Ø d 5 mm	308990 5
ER collet Nominal clamping Ø d 12 mm	309040 12
ER collet HP Nominal clamping Ø d 21 mm	309379 21
ER colletwith seal Nominal clamping Ø d 16 mm	308992 16
ER collet Nominal clamping Ø d 23 mm	308990 23
ER collet for machine tapswith seal Nominal clamping Ø d 7 mm	309419 7
ER chuck key for ER collet chuck 40	309680 40
ER collet Nominal clamping Ø d 26 mm	308990 26
ER collet Nominal clamping Ø d 19 mm	309040 19
ER collet set 15 pieces 2–16 mm	309240
ER clamping nutHigh Speed for ER 40	309610 40
ER collet HP Nominal clamping Ø d 16 mm	309379 16
ER collet set 23 pieces 4–26 mm	309320
ER collet Nominal clamping Ø d 6 mm	309040 6
ER collet HP Nominal clamping Ø d 20 mm	309379 20
ER collet for machine tapswith seal Nominal clamping Ø d 12 mm	309419 12
Pull stud Hurco 90° with fitsealed suitable for steep tapers 40	308806 40
ER colletwith seal Nominal clamping Ø d 6 mm	308992 6
ER collet HP Nominal clamping Ø d 17 mm	309379 17
Pull stud 45°sealed suitable for steep tapers 40	308765 40
ER collet Nominal clamping Ø d 11 mm	309040 11
ER collet Nominal clamping Ø d 22 mm	308990 22
ER collet for machine tapswith seal Nominal clamping Ø d 14 mm	309419 14
ER collet for machine tapswith seal Nominal clamping Ø d 11 mm	309419 11
ER collet HPwith seal and spray nozzles Nominal clamping Ø d 12 mm	309381 12

ER clamping nut for HiRunER collet chucks for ER 40	309617 40
Pull stud sealed, form A suitable for steep tapers 40	308610 40
Pull stud Hurco 45° with fit sealed suitable for steep tapers 40	308802 40
ER collet for machine taps with seal Nominal clamping Ø d 6 mm	309419 6
Pull stud Mori-Seiki, sealed, form A suitable for steep tapers 40	308630 40
ER collet for machine taps with seal Nominal clamping Ø d 22 mm	309419 22
ER collet Nominal clamping Ø d 13 mm	309040 13
ER collet HP Nominal clamping Ø d 25 mm	309379 25
ER collet HP with seal and spray nozzles Nominal clamping Ø d 25 mm	309381 25
ER collet HP Nominal clamping Ø d 9 mm	309379 9
ER collet Nominal clamping Ø d 15 mm	309040 15
ER collet HP Nominal clamping Ø d 19 mm	309379 19
ER collet HP Nominal clamping Ø d 23 mm	309379 23
ER collet Nominal clamping Ø d 11 mm	308990 11
ER collet Nominal clamping Ø d 17 mm	309040 17
ER collet Nominal clamping Ø d 18 mm	309040 18
ER collet Nominal clamping Ø d 22 mm	309040 22
ER collet with seal Nominal clamping Ø d 12 mm	308992 12
ER collet HP Nominal clamping Ø d 8 mm	309379 8
ER collet for machine taps with seal Nominal clamping Ø d 20 mm	309419 20
ER collet with seal Nominal clamping Ø d 8 mm	308992 8
ER collet Nominal clamping Ø d 20 mm	308990 20
ER collet for machine taps with seal Nominal clamping Ø d 10 mm	309419 10
ER collet with seal Nominal clamping Ø d 10 mm	308992 10
Pull stud sealed, form B suitable for steep tapers 40	308620 40

ER plain bearing clamping nut for ER 40	309612 40
ER collet HP Nominal clamping Ø d 24 mm	309379 24
ER collet HP Nominal clamping Ø d 5 mm	309379 5
ER collet set 23 pieces 4–26 mm	309028
ER collet Nominal clamping Ø d 13 mm	308990 13
ER colletwith seal Nominal clamping Ø d 22 mm	308992 22
ER collet Nominal clamping Ø d 16 mm	309040 16
ER collet HP Nominal clamping Ø d 7 mm	309379 7
Pull studsealed suitable for steep tapers 40	308635 40
ER clamping nut for ER 40	309580 40
Wrench for pull studsISO 7388 suitable for ISO taper size 40	308830 40
Pull studMori-Seiki, sealed, form A suitable for steep tapers 40	308625 40
ER collet Nominal clamping Ø d 19 mm	308990 19
ER collet Nominal clamping Ø d 7 mm	308990 7
ER collet HP Nominal clamping Ø d 6 mm	309379 6
ER collet HP Nominal clamping Ø d 11 mm	309379 11
ER collet HP Nominal clamping Ø d 14 mm	309379 14
ER collet HP Nominal clamping Ø d 22 mm	309379 22
ER colletwith seal Nominal clamping Ø d 14 mm	308992 14
ER collet for machine tapswith seal Nominal clamping Ø d 25 mm	309419 25
ER collet Nominal clamping Ø d 15 mm	308990 15
Pull stud, 18CrNiMo7Form A suitable for steep tapers 40	308605 40
ER collet Nominal clamping Ø d 10 mm	309040 10
ER collet Nominal clamping Ø d 8 mm	308990 8
ER collet for machine tapswith seal Nominal clamping Ø d 16 mm	309419 16
ER collet HP Nominal clamping Ø d 12 mm	309379 12
ER collet Nominal clamping Ø d 8 mm	309040 8

Pull stud 90°sealed suitable for steep tapers 40	308790 40
ER collet Nominal clamping Ø d 9 mm	308990 9
ER collet HP Nominal clamping Ø d 18 mm	309379 18
ER collet Nominal clamping Ø d 21 mm	308990 21
ER collet for machine tapswith seal Nominal clamping Ø d 8 mm	309419 8
ER colletwith seal Nominal clamping Ø d 18 mm	308992 18
Pull stud 90°sealed suitable for steep tapers 40	308795 40
ER collet Nominal clamping Ø d 18 mm	308990 18
ER collet HP Nominal clamping Ø d 15 mm	309379 15
ER collet Nominal clamping Ø d 21 mm	309040 21
ER collet Nominal clamping Ø d 23 mm	309040 23
ER collet HP Nominal clamping Ø d 3 mm	309379 3
ER collet HP Nominal clamping Ø d 4 mm	309379 4