

Garant**VBMT indexable insert for finishing 50 pieces, HB7130-2, Size: 110302****Order data**

Order number	GG3556 110302
GTIN	4067263092278
Item class	GGN

Technical description

Corner radius	0.2 mm
Contents	261142 HB7130-2
Number of changes/inserts	2
Cutting depth a_p	0.2 - 1.5 mm
Quantity	50
Cutting depth $a_{p \max}$	1.75 mm
Tool material	Carbide
ISO code indexable insert	VBMT 110302
Cutting depth $a_{p \min}$	0.15 mm
Main application	M
Finishing/roughing assignment	Finishing
Cutting speed v_c main application	80 - 270 mm/min
Feed f	0.1 - 0.3 mm/rev.

Type	HB7130-2
Cutting conditions	slightly interrupted
Chip breaker	VS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG3556 110302