

Garant**VBMT indexable insert for finishing 50 pieces, HB7130-2, Size: 110304****Order data**

Order number	GG3556 110304
GTIN	4067263092278
Item class	GGN

Technical description

Main application	M
Cutting depth a_p	0.2 - 1.5 mm
ISO code indexable insert	VBMT 110304
Finishing/roughing assignment	Finishing
Cutting depth $a_{p \min}$	0.25 mm
Feed f	0.1 - 0.3 mm/rev.
Cutting speed v_c main application	80 - 270 mm/min
Quantity	50
Cutting depth $a_{p \max}$	1.75 mm
Tool material	Carbide
Number of changes/inserts	2
Contents	261144 HB7130-2
Corner radius	0.4 mm

Type	HB7130-2
Cutting conditions	slightly interrupted
Chip breaker	VS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG3556 110304