

Garant**VBMT indexable insert for finishing 50 pieces, HB7130-2, Size: 160408****Order data**

Order number	GG3556 160408
GTIN	4067263092278
Item class	GGN

Technical description

Quantity	50
Cutting depth a_p	0.2 - 1.5 mm
ISO code indexable insert	VBMT 160408
Number of changes/inserts	2
Tool material	Carbide
Corner radius	0.8 mm
Contents	261154 HB7130-2
Cutting depth $a_{p \min}$	0.55 mm
Cutting depth $a_{p \max}$	2.5 mm
Finishing/roughing assignment	Finishing
Feed f	0.1 - 0.3 mm/rev.
Cutting speed v_c main application	80 - 270 mm/min
Main application	M

Data sheet

Type	HB7130-2
Cutting conditions	slightly interrupted
Chip breaker	VS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG3556 160408