

**VCMT 160404, Grade: HB7010**

Order data

Order number	261372 HB7010
GTIN	4045197671400
Item class	21G

Description

VCMT 160404 HB7010 Grade: HB7010

Chip breaker: SS

Cutting depth a_p : 0.2 - 1 mm

Feed f : 0.05 - 0.2 mm/rev.

Cutting speed v_c main application: 110 - 330 m/min

Technical description

Indexable insert clearance angle	degrees
Product name attribute	
Insert assignment	neutral
Rake	degrees
Shim	
Indexable insert profile	
Type of product	