

Garant**WNMG indexable insert for medium machining 30 pieces, HB7130-2, Size: 060408****Order data**

Order number	GG2983 060408
GTIN	4067263094913
Item class	GGN

Technical description

Number of changes/inserts	6
Finishing/roughing assignment	Finishing
Cutting depth a_p	0.5 - 4 mm
Cutting depth $a_{p \max}$	2 mm
Quantity	30
Cutting speed v_c main application	70 - 240 mm/min
Tolerance	M
Main application	M
Feed f	0.1 - 0.5 mm/rev.
Contents	252064 HB7130-2
Corner radius	0.8 mm
ISO code indexable insert	WNMG 060408
Cutting depth $a_{p \min}$	0.55 mm
Tool material	Carbide

Type	HB7130-2
Cutting conditions	slightly interrupted
Chip breaker	VM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2983 060408