

**VCMT 160404, Grade: HB7025****Order data**

| | |
|--------------|---------------|
| Order number | 261372 HB7025 |
| GTIN | 4045197671424 |
| Item class | 21G |

Description

VCMT 160404 HB7025 Grade: HB7025
Chip breaker: SS
Cutting depth a_p : 0.2 - 1 mm
Feed f : 0.05 - 0.2 mm/rev.
Cutting speed v_c main application: 60 - 280 m/min

Technical description

| | |
|----------------------------------|---------|
| Indexable insert clearance angle | degrees |
| Product name attribute | |
| Insert assignment | neutral |
| Rake | degrees |
| Shim | |
| Indexable insert profile | |
| Type of product | |