



Value pack VNMG indexable insert medium machining 30 pieces HBT020

Order data

Order number	GG3924 160404
GTIN	4067263843795
Item class	GGN

Technical description

Cutting depth $a_{p \min}$	0.25 mm
Contents	251828 HBT020
Feed f	0.1 - 0.45 mm/rev.
Coating	TiCN
Finishing/roughing assignment	Finishing
Corner radius	0.4 mm
Cutting depth $a_{p \max}$	2.5 mm
Tool material	Carbide
Number of changes/inserts	4
Cutting depth a_p	0.8 - 4 mm
Main application	P
Cutting speed v_c main application	100 - 280 mm/min
ISO code indexable insert	VNMG 160404
Quantity	30
Type	HBT020
Cutting conditions	slightly interrupted
Chip breaker	PM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG3924 160404
