



VCMT indexable insert for medium machining 30 pieces, HB7010-2, Size: 110304



Order data

Order number	GG2870 110304
GTIN	4067263092278
Item class	GGN

Technical description

Main application	P
Cutting depth a_p	0.3 - 2 mm
Cutting speed v_c main application	120 - 440 mm/min
Finishing/roughing assignment	Finishing
Tolerance	M
Cutting depth $a_{p \min}$	0.25 mm
Cutting depth $a_{p \max}$	1.75 mm
Number of changes/inserts	2
Contents	261454 HB7010-2
Feed f	0.08 - 0.3 mm/rev.
Tool material	Carbide
Corner radius	0.4 mm
ISO code indexable insert	VCMT 110304

Data sheet

Quantity	30
Type	HB7010-2
Cutting conditions	continuous
Chip breaker	SM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2870 110304