



VCMT indexable insert for medium machining 30 pieces, HB7020-2, Size: 160408



Order data

Order number	GG2871 160408
GTIN	4067263096016
Item class	GGN

Technical description

Finishing/roughing assignment	Finishing
Corner radius	0.8 mm
Number of changes/inserts	2
Cutting speed v_c main application	110 - 350 mm/min
Cutting depth $a_{p \min}$	0.55 mm
Feed f	0.08 - 0.3 mm/rev.
Tolerance	M
ISO code indexable insert	VCMT 160408
Cutting depth $a_{p \max}$	2.5 mm
Tool material	Carbide
Contents	261459 HB7020-2
Main application	P
Cutting depth a_p	0.3 - 2 mm

Data sheet

Quantity	30
Type	HB7020-2
Cutting conditions	slightly interrupted
Chip breaker	SM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2871 160408