

**Garant**
**VCGT 160402, Grade: HB7310**


### Order data

Order number	261457 HB7310
GTIN	4045197671707
Item class	21G

### Description

VCGT 160402 HB7310 Grade: HB7310  
 Chip breaker: AM  
 Tolerance: G  
 Cutting depth  $a_p$ : 0.1 - 4 mm  
 Feed  $f$ : 0.05 - 0.5 mm/rev.  
 Cutting speed  $v_c$  main application: 350 - 600 m/min

### Technical description

Main application	N
Cutting conditions	continuous
Cutting speed $v_c$ main application	350 - 600 m/min
Corner radius	0.2 mm
Chip breaker	AM
Feed $f$	0.05 - 0.5 mm/rev.

Cutting depth $a_p$	0.1 - 4 mm
Grade	HB7310
Finishing/roughing assignment	Roughing
Finishing/roughing assignment	Finishing
Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Tool material	Carbide
ISO code indexable insert	VCGT 160402
Number of changes/inserts	2
Tolerance	G
Type of product	Indexable insert for turning