

Garant**VBMT indexable insert for medium machining 30 pieces, HB7140-2, Size: 110304****Order data**

Order number	GG3560 110304
GTIN	4067263092278
Item class	GGN

Technical description

Cutting depth a_p	0.5 - 2.5 mm
ISO code indexable insert	VBMT 110304
Coating	coated
Corner radius	0.4 mm
Contents	261224 HB7140-2
Number of changes/inserts	2
Cutting speed v_c main application	60 - 200 mm/min
Cutting depth $a_{p \min}$	0.25 mm
Tool material	Carbide
Feed f	0.1 - 0.4 mm/rev.
Main application	M
Finishing/roughing assignment	Finishing
Cutting depth $a_{p \max}$	1.75 mm

Tolerance	M
Quantity	30
Type	HB7140-2
Cutting conditions	heavily interrupted
Chip breaker	VM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG3560 110304