



Value pack WNMG indexable insert medium machining 30 pieces HBT020

Order data

Order number	GG3928 060408
GTIN	4067263093657
Item class	GGN

Technical description

ISO code indexable insert	WNMG 060408
Contents	252093 HBT020
Corner radius	0.8 mm
Number of changes/inserts	6
Main application	P
Coating	TiCN
Cutting depth $a_{p \max}$	2 mm
Cutting depth $a_{p \min}$	0.55 mm
Finishing/roughing assignment	Finishing
Tool material	Carbide
Cutting speed v_c main application	100 - 280 mm/min
Cutting depth a_p	0.8 - 5 mm
Feed f	0.1 - 0.45 mm/rev.
Quantity	30
Type	HBT020
Cutting conditions	slightly interrupted
Chip breaker	PM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG3928 060408
