

**Value pack DNMG indexable insert medium machining 30 pieces HB7020-2****Order data**

|              |                |
|--------------|----------------|
| Order number | GG2438 160405R |
| GTIN         | 4067263094555  |
| Item class   | GGN            |

**Technical description**

|                                      |                              |
|--------------------------------------|------------------------------|
| Contents                             | 251030 HB7020-2              |
| Main application                     | P                            |
| Cutting speed $v_c$ main application | 130 - 370 mm/min             |
| Number of changes/inserts            | 2                            |
| Tool material                        | Carbide                      |
| Cutting depth $a_{p \min}$           | 0.35 mm                      |
| Cutting depth $a_p$                  | 0.3 - 4 mm                   |
| Cutting depth $a_{p \max}$           | 4 mm                         |
| Feed $f$                             | 0.2 - 0.5 mm/rev.            |
| Finishing/roughing assignment        | Finishing                    |
| Quantity                             | 30                           |
| Type                                 | HB7020-2                     |
| Cutting conditions                   | slightly interrupted         |
| Chip breaker                         | SM                           |
| Type of product                      | Indexable insert for turning |

**Suitable products**

No Shop URL available for: GG2438 160405R

