

**Garant****VC.T 110304, Grade: HB7310**

## Order data

Order number	261454 HB7310
GTIN	4045197671660
Item class	21G

## Description

## Technical description

Cutting conditions	continuous
Cutting speed $v_c$ main application	350 - 600 m/min
Cutting depth $a_p$	0.1 - 4 mm
Corner radius	0.4 mm
Chip breaker	AM
Feed $f$	0.05 - 0.5 mm/rev.
Main application	N
Grade	HB7310
Finishing/roughing assignment	Finishing
Tool material	Carbide

ISO code indexable insert	VCGT 110304
Number of changes/inserts	2
Tolerance	G
Type of product	Indexable insert for turning