

**Garant****VC.T 160408, Grade: HU7310**

## Order data

Order number	261459 HU7310
GTIN	4045197672025
Item class	21G

## Description

## Technical description

Cutting speed $v_c$ main application	350 - 600 m/min
Corner radius	0.8 mm
Feed $f$	0.05 - 0.5 mm/rev.
Cutting depth $a_p$	0.1 - 4 mm
Cutting conditions	continuous
Chip breaker	AM
Main application	N
Grade	HU7310
Finishing/roughing assignment	Finishing
Tool material	Carbide

Coating	uncoated
ISO code indexable insert	VCGT 160408
Number of changes/inserts	2
Tolerance	G
Type of product	Indexable insert for turning